

EADR 20

Connection thread gasket, EPDM



Product illustrations are exemplary and may differ from the chosen product. Further variants and individual customization, we will gladly provide you on request.

SPRINT

hategen

RoHS

Material	EPDM
Temp. range min	-40 °C
Temp. range max	140 °C
Thread type	M
Ø Connection thread D	20
Lead	1,5
Total length TL	2 mm
Product Color	RAL 9005
Order no. RAL 9005	10062803
Type	EADR 20
Packing unit	100
ETIM-Classification	EC000441

19.06.2017