

## EADR 40

Connection thread gasket, EPDM



Product illustrations are exemplary and may differ from the chosen product. Further variants and individual customization, we will gladly provide you on request.

**SPRINT**

**hätogen**



<b>Material</b>	EPDM
<b>Temp. range min</b>	-40 °C
<b>Temp. range max</b>	140 °C
<b>Thread type</b>	M
<b>Ø Connection thread D</b>	40
<b>Lead</b>	1,5
<b>Total length TL</b>	2 mm
<b>Product Color</b>	RAL 9005
<b>Order no. RAL 9005</b>	10062806
<b>Type</b>	EADR 40
<b>Packing unit</b>	100
<b>ETIM-Classification</b>	EC000441

19.06.2017