

Product Description

Fast assembly; Easy to disassemble; No slack in the conduit; No loose parts



Application range

- In combination with protective conduit
- SILVYN® FPAS
- Fastening of conduits on machine walls for all applications

Benefits

- Fast assembly
- Easy to disassemble
- No slack in the conduit
- No loose parts

Design

- One-piece conduit holder with borehole for fixation

Note

- UV-resistant and weather-resistant

Product features

- Removeable with a screwdriver
- One-piece conduit holder



Technical Data

Colour delivered

Black (RAL 9005), UV-resistant Grey (RAL 7001)

Temperature range

-50°C to +135°C

Material

PA66 Halogen-free

Article List

Part number	Article designation	Hole Ø (mm)	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FCL black				
55506905	10	5	10	10
55506915	13	5	13	10
55506925	16	5	16	10
55506985	18	6	18	10
55506935	21	6	21	10
55506945	28	6	28	10
55506955	34	6	34	10
55506965	42	6	42	5
55506975	54	6	54	5
SILVYN® FCL grey				
55506900	10	5	10	10
55506910	13	5	13	10
55506920	16	5	16	10
55506980	18	6	18	10
55506930	21	6	21	10
55506940	21	6	21	10
55506950	21	6	21	10
55506960	42	6	42	5
55506970	54	6	54	5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.