



HelaGuard Metallic Conduits with Metallic Overbraid and Fittings

Fittings for metallic conduits and metallic overbraid

• SCSB-PC Plain Hole Connector

Plain hole connector, nickel plated brass.

Features and Benefits

- Two part fitting comprising shell and body without thread
- The body is fitted to the conduit through the opposite side of the entry
- Acts as a locking device
- Provides a smooth entry bush

Technical Table

Article-No.	Type	Nominal Ø	Pack Cont.
166-34800	SCSB12-PC	12	10
166-34801	SCSB16-PC	16	10
166-34802	SCSB20-PC	20	10
166-34803	SCSB25-PC	25	10
166-34804	SCSB32-PC	32	2
166-34805	SCSB40-PC	40	1

All dimensions in mm. Subject to technical changes.



HelaGuard SCSB-PC Plain Hole Connector.

Material Data

Material	Nickel Plated Brass (NPB)
Colour	Metal (ML)
Operating Temperature	-100 °C to +300 °C

