

Pipe Surface Thermocouples



For pipe temperature measurement up to 350°C. They are available in a number of sizes to suit your diameter of pipe. These sensors make direct contact with the pipe for maximum performance and have grounded tips for a fast response.

- Stainless steel pipe clamp sensor with adjustable diameter
- Available in thermocouple type K or J
- Fits pipe diameters 30-45mm and 40-55mm
- Grounded tip for fast response
- Rated up to 350°C
- Fitted with 2 metres of Glassfibre stainless steel braided extension cable, 7/0.2mm

T/C Type	To Fit Pipe Diameter	Manufacturer's Part Number	Rapid Part Number
J	30-45mm	XE-3912-001	61-3189
J	40-55mm	XE-3913-001	61-3190
K	30-45mm	XE-3916-001	61-3191
K	40-55mm	XE-3917-001	61-3192