

Product information

26 26 200 T

Snipe Nose Side Cutting Pliers (Stork Beak Pliers)

DIN ISO 5745 IEC 60900 DIN EN 60900

- Elastic tips: dimensionally stable even when twisted
- Pliers with integrated, insulated tether attachment point for a tool tether
- Distortion-tolerant, elastic precision tips
- Half-round, long, tapered jaws
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	26 26 200 T
EAN	4003773081456
Pliers	chrome plated
Head	chrome plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
weight	215 g
Dimensions	200 x 54 x 27 mm
Standard	DIN ISO 5745 DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

	Ø 3.2 mm
	Ø 2.2 mm
	9.5 mm
Tips width (W4)	3.0 mm
Tips thickness (T2)	2.5 mm
Gripping surface length (L4)	23.0 mm
	73.0 mm
Head angle (L4)	40
Head width (W3)	18 mm
Style	2
Drop Protection System	yes
VDE tested	yes

Technical details



Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAC420c044
UNSPSC 13.1	27112134

technical change and errors excepted