

## Product information

# 95 16 165 T

## Cable Shears

IEC 60900 DIN EN 60900



⚡ 1000 V



- With integrated insulated tether attachment point for a tool tether
- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Clean and smooth cut without crushing and deformation
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- Easy cutting with one-hand operation
- With guard
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened

### General

Article No.	95 16 165 T
EAN	4003773081524
Shears	chrome plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
weight	260 g
Dimensions	165 x 67 x 28 mm
Standard	DIN EN 60900 IEC 60900
Reach	Nein
RohS	no

### Technical details

Style	1
Cutting capacity copper cable, multiple-stranded	50 mm <sup>2</sup>
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
AWG	1 / 0
Drop Protection System	yes
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001
UNSPSC 13.1	23241616

technical change and errors excepted



Cut performed with a Cable Shear: easy, clean cut without any deformation of the cable

