

Sku

Mechanical 3-leg pullers

Pullers

U.306-180 U.306 - Outside pullers



Description:

- Versatile: takes 2 or 3 legs. Converts into inside puller with the legs U.306G2 + screw U.306-4 or legs U.306G20 + screw U.306-2.
- Comfort: self-gripping legs by return spring. The puller stays in rolling position even when not in tension.
- Safety: legs locked in position on the bearing using a knob. No risk for the puller to escape from the bearing.
- Shear pin: the pin shears if torque limit is exceeded. Supplied with 2 spare pins.
- Set of 3 spare pins. Refer to spares table according to puller power.
- Adaptable puller accessories: slide hammer U.306M (direct attachment) and beam U.40 (attached using ring and nut U.306A1 to be ordered separately).
- The U.306-260 puller is supplied with the U.306-3 screw fitted with its extension.

C mini - maxi [mm]:	50 - 170
L x l x H [mm]:	135 x 285 x 320
P maxi [mm]:	200
Hex Size [mm]:	18
Legs:	U.306G10
Ton [t]:	4
Screw Size:	U.306-2
Screw Size [mm]:	18
T [kN]:	40
[kg]:	2,200

