

E.316A30R E.316A - Electronic torque / angle wrenches with ratchet**Description:**

- Accuracy:
 - Torque: $\pm 2\%$ between 20% and 100% wrench capacity.
 - Angle: $\pm 2^\circ$.
- End fitting: 9 x 12 and 14 x 18 mm.
- Measuring mode: peak or follower.
- Locking keypad (the operator has access only to program choices and result memorising).
- Measuring unit: N.m, lbf.ft, lbf.in, kg.cm and deg.
- Presetting possible of 9 torque and/or angle values.
- Memory 250 values with PC USB link.
- Supplied with calibration certificate.
- Supplied in plastic case and foam module.

L [mm]: 390

Capacity [N.m]: 1,5 - 30,0

Square ["]: 1/4

Ratchet: R.372

[kg]: 1,604
