

DIN Chassis Sockets

Order code: **20-0245** 3 pin Order code: **20-0255** 5 pin Order code: **20-0375** 6 pin

Specifications:


Rating: Insulation resistance: Dielectric strength: Voltage withstanding: Insertion force: Withdrawal force: Contact resistance: Operation temperature: Life cycle:

Materials:

Socket: Insulator: Contact pin: Rivet: 100V AC at 1A or 12V DC 2A maximum Over 100m IHM at 500V DC 250V Ac for one minute Ac 1000V for one minute 4. 0KG maximum 1-3. 5kg 20m Ohm maximum 5°C ~ 70°C 5000~10000 times

Nickel plated case PBT Silver plated brass Nickel plated aluminium





www.rapidonline.com