

Material & Finish:

Insulator material PBT glass re-inforced
Flame retardant to **UL94V-0**

Contact material:
plug Copper alloy gold over nickel plate
socket Phosphor bronze gold over nickel plate

Shell material Tin plated steel

Contact current rating 5A

Voltage rating 250V AC max.

Contact resistance 10mΩ max.

Insulation resistance 1x 10⁹Ω at 500V DC

Operating temperature -55°C to +150°C



| Order code | Type | A | B | C | D |
|------------|---------------|-------|-------|-------|-------|
| 15-0100 | 9 Way Male | 16.92 | 24.99 | 30.81 | 19.28 |
| 15-0150 | 9 Way Female | 16.33 | 24.99 | 30.81 | 19.28 |
| 15-0105 | 15 Way Male | 25.25 | 33.32 | 39.14 | 27.51 |
| 15-0155 | 15 Way Female | 24.66 | 33.32 | 39.14 | 27.51 |
| 15-0110 | 25 Way Male | 38.96 | 47.04 | 53.04 | 41.30 |
| 15-0160 | 25 Way Female | 38.38 | 47.04 | 53.04 | 41.30 |

