

Specifications:

Shell: Tin plated
 Insulator: PBT & 30% Glass-fibre UL-94-V0
 Contact: Phosphor bronze
 Plating: Gold plated over nickel
 Dielectric Strength: 1000V for one minute
 Insulator resistance: 1000MΩ min at 500V DC
 Temperature: -55°C ~ +105°C



Ways	Type	Order code	A	B	C	D
15	Plug (M)	15-0064	30.81	24.88	16.92	8.36
	Receptacle (F)	15-0095			24.66	7.90
44	Receptacle (F)	15-0062	53.04	47.04	38.38	7.90

