

Product information

83 61 015

Pipe Wrench S-Type

With fast adjustment

- Pinch guard prevents operators' fingers being pinched
- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- High wear resistance due to the additionally hardened teeth
- Maximum load capability thanks to completely hardened handles
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

| | |
|-------------|--------------------|
| Article No. | 83 61 015 |
| EAN | 4003773077619 |
| Pliers | grey powder-coated |
| Handles | plastic coated |
| weight | 1,470 g |
| Dimensions | 420 x 84 x 28 mm |
| Reach | no |
| RohS | no |

Technical details

| | |
|---------------------------------|---------|
| Clamping width | 60 mm |
| Capacities for pipes (diameter) | Ø 2 3/8 |
| Capacities for nuts | 60 mm |
| Inner diameter, inches | 1 Inch |

Classification

| | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040301 |
| ETIM 5.0 | EC000842 |
| ETIM 6.0 | EC000842 |
| proficl@ss 6.0 | AAC492c005 |
| UNSPSC 13.1 | 27111708 |

technical change and errors excepted

