

Product information

83 60 020

Pipe Wrench S-Type

With fast adjustment

DIN 5234

- Pinch guard prevents operators' fingers being pinched
- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- High wear resistance due to the additionally hardened teeth
- Maximum load capability thanks to completely hardened handles
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	83 60 020
EAN	4003773078838
Pliers	red powder-coated
weight	2,420 g
Dimensions	560 x 94 x 32 mm
Standard	DIN 5234
Reach	yes
RohS	no

Technical details	
Capacities for pipes (diameter)	Ø 2 3/4
Capacities for nuts	70 mm
Inner diameter, inches	2 Inch

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000842
ETIM 6.0	EC000842
proficl@ss 6.0	AAC492c005
UNSPSC 13.1	27111708

technical change and errors excepted

