

Product information

95 36 315 A

Cable Cutter

(ratchet action)

For steel wire armoured cables (SWA cable)

IEC 60900 DIN EN 60900



⚡ 1000 V  

Robust, handy, stable: for steel-armoured cables (SWA cables)

- Cuts through steel wire armoured cables with a diameter of up to 45 mm / 380 mm² (e.g. 4 x 95 mm²) using one or two-handed operation
- Sturdy. Easy to use. Stable.
- Simple handling due to low weight (800 g) and compact design (315 mm length) – can also be used in confined areas
- Precision-ground blades and induction-hardened cutting edges cut smoothly and neatly without crushing
- Innovative high leverage three-stage ratchet-drive
- Support area for putting down the pliers when cutting
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Cutter head: special high-grade tool steel, forged, oil-hardened

General

Article No.	95 36 315 A
EAN	4003773078579
Pliers	black lacquered
Handles	insulated with multi-component grips, VDE-tested
weight	800 g
Dimensions	315 x 140 x 30 mm
Standard	IEC 60900 DIN EN 60900
Reach	yes
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	380 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 45 mm
MCM	750
VDE tested	yes

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAC484c002
UNSPSC 13.1	23241616

Accessories

95 39 315 A01	Pivot cutter repair kit for 95 32 315 A and 95 36 315 A
95 39 315 A02	Fixed cutter repair kit for 95 32 315 A and 95 36 315 A

technical change and errors excepted



Precision-milled and induction-hardened cutting edge