

LOGO! 24RCO (AC), LOGIC MODULE, PU/I/O: 24V UC/24V UC/RELAY, 8 DI/4 DO; W/O DISPLAY, MEMORY 200 BLOCKS, EXPANDABLE WITH EXTRA MODULES



Installation type/mounting

Mounting on 35 mm DIN rail, 4 spacing units wide

Supply voltage

Rated value (DC)	Yes
• 24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Rated value (AC)	Yes
• 24 V AC	Yes

Line frequency

• permissible range, lower limit	47 Hz
• permissible range, upper limit	63 Hz

Time of day

Time switching clocks

• Number	8
• Power reserve	80 h

Digital inputs

Number of digital inputs	8
Digital outputs	
Number of digital outputs	4; Relays
Short-circuit protection	No; external fusing necessary
Relay outputs	
Switching capacity of contacts	
— with inductive load, max.	3 A
— with resistive load, max.	10 A
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	
• Marine approval	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Dimensions	
Width	72 mm
Height	90 mm
Depth	55 mm
last modified:	24.02.2016