

LOGO! AM2 EXPANSION MODULE, PU: DC 12/24V, 2 AI, 0 - 10V
OR 0/4 - 20mA FOR LOGO! 8



Installation type/mounting

Mounting on 35 mm DIN rail, 2 spacing units wide

Supply voltage

Rated value (DC)

- 12 V DC Yes; 10.8 V DC to 28.8 V DC
- 24 V DC Yes; 10.8 V DC to 28.8 V DC

Analog inputs

Number of analog inputs 2

Input ranges

- Voltage Yes
- Current Yes
- Resistance thermometer No

Input ranges (rated values), voltages

- 0 to +10 V Yes

Input ranges (rated values), currents

- 0 to 20 mA Yes; 0 mA or 4 mA to 20 mA

Input ranges (rated values), resistance thermometer

- Pt 100 No

EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	
• Marine approval	Yes
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Dimensions	
Width	35.5 mm
Height	90 mm
Depth	58 mm
last modified:	24.02.2016