



LOGO! contact 230 Switching module for direct switching of resistive loads up to 20 A and motors up to 4 kW, 230 V AC, 3 NO contacts+1 NC EAN: 4025515050759

Supply voltage			
Rated value (AC)			
• 230 V AC	Yes		
Line frequency			
• permissible range, lower limit	47 Hz		
• permissible range, upper limit	63 Hz		
Standards, approvals, certificates			
CE mark	Yes		
Ambient conditions			
Ambient temperature during operation			
• min.	-25 °C		
• max.	55 °C		
Dimensions			
Width	36 mm		
Height	72 mm		
Depth	55 mm		
Weights			
Weight, approx.	160 g		
Classifications			
		Version	Classification
	eClass	14	27-24-22-16
	eClass	12	27-24-22-16
	eClass	9.1	27-24-22-16
	eClass	9	27-24-22-16
	eClass	8	27-24-22-16
	eClass	7.1	27-24-22-16
	eClass	6	27-24-22-16
	ETIM	10	EC001417
	ETIM	9	EC001417
	ETIM	8	EC001417
	ETIM	7	EC001417
	IDEA	4	3565
	UNSPSC	15	32-15-17-05
Approvals / Certificates			
General Product Approval		Maritime application	other

[Manufacturer Declaration](#)



[Manufacturer Declaration](#)



[Confirmation](#)

last modified:

5/22/2024