



## Main

Range	PowerLogic
Product name	PowerLogic PM5000
Device short name	PM5110
Product or component type	Power meter

## Complementary

Power quality analysis	Up to the 15th harmonic
Device application	Power monitoring
Type of measurement	Energy Active and reactive power Voltage Current Frequency Power factor
[Us] rated supply voltage	100...415 V AC (45...65 Hz) 125...250 V DC
Network frequency	50 Hz 60 Hz
[In] rated current	5 A 1 A
Poles description	3P + N 3P 1P + N
Power consumption in VA	10 VA at 415 V
Display type	Backlit LCD
Display resolution	128 x 128 pixels
Sampling rate	64 samples/cycle
Measurement current	10 mA...9 A
Analogue input type	Current (impedance 0.3 mOhm) Voltage (impedance 5 MOhm)
Measurement voltage	35...690 V AC 45...65 Hz between phases

20...400 V AC 45...65 Hz between phase and neutral

Frequency measurement range	45...65 Hz
Number of inputs	0
Measurement accuracy	+/- 0.5 % active energy +/- 2 % reactive energy +/- 0.5 % active power +/- 0.5 % apparent power +/- 0.05 % frequency +/- 0.005 % power factor +/- 0.5 % current +/- 0.5 % voltage
Accuracy class	Class 0.5S (active energy according to IEC 62053-22)
Number of outputs	1 digital
Communication port protocol	Modbus RTU and ASCII 2 wires, : 9.6, 19.2 and 38.4 kbauds, even/odd or none, insulation: 2500 V JBUS
Communication port support	RS485
Data recording	Min/Max of instantaneous values Time stamping
Mounting mode	Flush-mounted
Mounting support	Framework
Standards	IEC 61557-12 EN 50470-3 IEC 62053-24 IEC 60529 EN 50470-1 IEC 62053-22 UL 61010-1
Product certifications	CE conforming to IEC 61010-1 CULus conforming to UL 61010-1
Width	96 mm
Depth	72 mm
Height	96 mm
Product weight	380 g

## Environment

Electromagnetic compatibility	<ul style="list-style-type: none"><li>• conducted and radiated emissions class class B, conforming to EN 55022</li><li>• limits for harmonic current emissions class class A, conforming to IEC 61000-3-2</li><li>• electrostatic discharge class level 4, conforming to IEC 61000-4-2</li><li>• conducted RF disturbances class level 3, conforming to IEC 61000-4-6</li><li>• magnetic field at power frequency class level 4, conforming to IEC 61000-4-8</li></ul>
IP degree of protection	IP52 (front) conforming to IEC 60529 IP30 (body) conforming to IEC 60529
Relative humidity	5...95 % 50 °C
Pollution degree	2
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Operating altitude	2000 m

## Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------