



Main

Range	Acti 9
Product name	Acti 9 iEM3000
Device short name	IEM3110
Product or component type	Energy meter

Complementary

Poles description	1P + N 3P 3P + N
Type of measurement	Active energy
Device application	Sub billing Partial meter
Accuracy class	Active energy : class 1 according to IEC 62053-21 Active energy : class B according to EN 50470-3 Active energy : class 1 according to IEC 61557-12
Analogue input type	Direct input
[In] rated current	63 A
Rated voltage	100...277 V 173...480 V
Network frequency	50 Hz 60 Hz
Technology type	Electronic
Display type	LCD display
Sampling rate	32 samples/cycle
Measurement current	<= 63 A
Maximum value measured	99999999.9 kWh
Communication port protocol	-
Communication port support	-
Local signalling	Power ON : indicator light (green) Accuracy checking : flashing LED (yellow)
Number of inputs	0
Number of outputs	1 pulse
Mounting mode	Clip-on
Mounting support	DIN rail
Connections - terminals	Screw terminals 16 mm ²
Overvoltage category	III
Standards	IEC 61036 IEC 61557-12 IEC 62053-21 IEC 62053-23 IEC 61010 UL 61010-1
Product certifications	UL EAC (sub-meter) CE - IEC 61010 (safety) CE - IEC 61326-1 (EMC) CULus - ANSI C12.20 (sub-meter)

MID - EN 62052 (sub-meter)
RCM - NMI M 6-1 (sub-meter)
MID - EN 50470-3 (sub-meter)
CE - EN 61557-12 (power monitor)
CULus - UL 61010 (safety)

Environment

IP degree of protection	IP40 (front panel) conforming to IEC 60529 IP20 (body) conforming to IEC 60529
pollution degree	2
relative humidity	5...95 % at 50 °C
ambient air temperature for operation	-25...60 °C (NMI) -25...60 °C (IEC) -25...55 °C (MID)
ambient air temperature for storage	-40...85 °C
operating altitude	< 2000 m
colour	White
9 mm pitches	10
width	90 mm
height	95 mm
depth	69 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1214 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------