



### Main

Range of product	Easy9
Product or component type	Empty consumer unit
Enclosure type	Metal enclosure
Provided equipment	Earth/neutral terminal block Busbar
Type of front cover	Plain
Product compatibility	Easy9 MCB Easy9 RCCB Easy9 RCBO Easy9 switch Easy9 SPD

### Complementary

Enclosure mounting	Flush Surface
Number of 18 mm modules per row	12
Total number of 18 mm modules	12
Number of horizontal rows	1
Number of ways	12 ways
Enclosure material	Metal
[In] rated current	100 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Type of rail	DIN
Cable entry	Knock-out
Cable cross section	1...25 mm <sup>2</sup> incoming
Comb busbar and distribution block compatibility	YES
Product weight	5.85 kg
Height	276.8 mm
Width	392.8 mm
Depth	119.55 mm
Colour	White ( RAL 9003 )

### Environment

standards	BS EN 61439-3 BS 7671: amendment 3
standards	BS EN 61439-3
IP degree of protection	IPxx D on top IP3x with cover
IK degree of protection	IK05
overvoltage category	II

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.