



## Main

|                           |  |
|---------------------------|--|
| Range                     | Spacial  |
| Product name              | Spacial SBM  |
| Device application        | Multi-purpose                                      |
| Product or component type | Industrial box                                     |
| Device short name         | SBM  |
| Enclosure type            | Flat face box                                      |
| Enclosure nominal height  | 200 mm   |
| Enclosure nominal width   | 200 mm   |
| Enclosure nominal depth   | 120 mm   |
| Enclosure mounting        | Wall mounted                                       |
| Device composition        | 1 x body<br>1 x cover<br>4 x cover screw           |
| Body type                 | Single piece body folded and welded                |
| Type of front cover       | Plain door   |
| Cover fixing              | Half turn metal screw                              |
| Lock type                 | Outside sealed area: PZ2 screwdriver captive screw |
| Removable parts           | Cover, by captive screws                           |

## Complementary

|                                       |                              |
|---------------------------------------|------------------------------|
| Material                              | Sheet steel                  |
| Surface finish                        | Polyester powder             |
| Colour                                | Grey ( RAL 7035 )            |
| Standards                             | IEC 62208                    |
| Product certifications                | BV<br>DNV<br>GL<br>LR<br>UL  |
| IP degree of protection               | IP66 IEC 60529               |
| IK degree of protection               | IK10 conforming to IEC 62262 |
| Ambient air temperature for storage   | -35...60 °C                  |
| Ambient air temperature for operation | -35...80 °C                  |

## Environment

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1241 - Schneider Electric declaration of conformity |
| REACH                            | Reference not containing SVHC above the threshold                     |
| Product environmental profile    | Available   |
| Product end of life instructions | Need no specific recycling operations                                 |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|