

## GMC132SS

Exclusive Metal clad - switched socket - 13 A - 230 V  
- 2 gangs - grey



### Main

Range of product	Exclusive
Aesthetic name	Metal clad
Product or component type	Switched socket
Device presentation	Complete product
Outlet standard	British
Colour tint	Matt grey
Quantity per set	Set of 5

### Complementary

Switch function	1-pole
Rated current	13 A, 230 V AC 50 Hz :
Actuator	Rocker
Number of gangs	2 gangs
Pilot light	Without neon indicator
Fixing mode	By screws
Connections - terminals	Screw terminals
Material	Powder coated steel
Type of installation	Indoor
Depth	42 mm
Width	139 mm
Height	79 mm
Product weight	0.434 kg

### Environment

standards	BS 1363
IP degree of protection	IP20

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be Compliant on 1Q2016 Will be Compliant on 1Q2016
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------