



Main

Range of product	Mureva BOX
Product or component type	Junction box
Colour tint	Grey RAL 7035
Quantity per set	1 piece

Complementary

Wiring device mounting	Surface
Cable entry	Grommets
Fixing mode	Screw-fixed cover
Base dimension	150 x 105 x 80 mm
Cable entry number	10 grommets Ø 25 mm
Material	PP (polypropylene) cover SBS (styrene butadiene styrene) grommet
Electrical insulation class	Class II according to IEC 536
Height	85 mm
Width	165 mm
Depth	125 mm
Product weight	0.29 kg

Environment

ambient air temperature for operation	-25...40 °C
IP degree of protection	IP55 according to IEC 60529
IK degree of protection	IK07 according to EN 50102
fire resistance	750 °C
standards	EN 60670
product certifications	CE
environmental characteristic	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1026 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------