

## GMC1012

Exclusive - 2-way plate switch - 1 gang - 10 AX - grey



### Main

Product or component type	Plate switch
Device presentation	Complete product
Colour tint	Grey
Quantity per set	Set of 10

### Complementary

Switch function	2-way
Control type	Rocker
Number of gangs	1 gang
Pilot light	Without neon indicator
Device mounting	Wall mounted
Rated current	10 AX 230 V AC
Connections - terminals	Screw terminals
Material	Powder coated steel
Surface finish	Matt
Height	79 mm
Width	79 mm
Depth	42 mm
Product weight	0.254 kg

### Environment

standards	BS EN 60669-1
IP degree of protection	IP20

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be Compliant on 4Q2016 Will be Compliant on 4Q2016
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------