



Main

Range	Easy9
Product or component type	Consumer unit equipped
Provided equipment	1 miniature circuit breaker (MCB) 6 A 1 miniature circuit breaker (MCB) 16 A 1 RCCB 63 A
Product compatibility	Easy9 switch Easy9 MCB Easy9 RCBO Easy9 RCCB Easy9 SPD
Number of 18 mm modules per row	2

Complementary

Enclosure type	Metal enclosure
Enclosure mounting	Surface
Type of front cover	Plain
Total number of 18 mm modules	2
Number of horizontal rows	1
Number of ways	2
Network frequency	50 Hz
Type of rail	DIN
Cable entry	Knock-out
Cable cross section	1...25 mm ²
[In] rated current	100 A
[Ue] rated operational voltage	230/240 V
Enclosure material	Metal
Height	276.8 mm
Width	212.8 mm
Depth	119.55 mm
Colour	White (RAL 9003)
Product weight	3.899 kg

Environment

Standards	BS EN 61439-3 BS 7671: amendment 3
IP degree of protection	IPxx D on top IP3x with cover
IK degree of protection	IK05
Overvoltage category	II