



## Main

Range	Thorsman
Product name	Thorsman 30 LED
Product or component type	Work lamp
Light source	SMD LED 5630 30 W

## Complementary


Type of installation	Outdoor Indoor
[Ue] rated operational voltage	100...240 V
Network type	AC
Network frequency	50/60 Hz
Plug pole configuration	2P + E
Plug standard	UK
Outlet standard	United Kingdom
Number of power socket outlets	1 x
Luminous flux	2850 lm
Bulb lifespan	50000 h
Colour rendering index	Ra=80
Colour temperature	4500 K
Beam angle	100 °
Cable insulation material	Neoprene
Material	ABS (acrylonitrile butadiene-styrene) TPE (thermoplastic elastomer)
Electrical connection	2 m H07RN-F3G1.5 mm <sup>2</sup> power cord
Height	250 mm
Width	256 mm
Depth	109 mm
Product weight	1.775 kg

## Environment

Environmental characteristic	Splashproof Dustproof
------------------------------	--------------------------

IP degree of protection	IP54
IK degree of protection	IK07
Quality labels	CE
Ambient air temperature for operation	-25...40 °C

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1642 - Schneider Electric declaration of conformity  <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations