



Main

Range of product	KNX
Product or component type	Power supply
Bus type	KNX

Complementary

Condition of use	Other device KNX device
Function of module	With output voltage stabilized
Mounting support	DIN rail
Rated operational power in W	9.6 W
Output current	0.4 A
Output voltage	24 V
Connections - terminals	Screw terminals
Height	68.1 mm
Width	17.5 mm
Depth	68.1 mm

Environment

IP degree of protection	IP20
Environmental health and issues	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0647 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available

 [Product environmental](#)

Product end of life instructions

Available

 [End of life manual](#)

Contractual warranty

Warranty period

18 months
