



### Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	Easypact CVS PowerPact Multistandard Compact NSX
Voltage release type	Shunt trip release
[Uc] control circuit voltage	220...240 V AC 208...277 V AC

### Complementary

Control signal type	Impulse Maintained
Impulse duration	$\geq 20$ ms
Threshold tripping voltage	$0.7 \dots 1.1 \times U_n$ - during opening time
Supply inrush power	30 W
Mounting mode	Fixed
Response time	50 ms
Auxiliary connection terminal	Screw terminal $0 \dots 1.5 \text{ mm}^2$

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0938 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product environmental</a>

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---