



MCB 10kA 4-pole C-characteristics

Miniature circuit breaker 10kA ideal for industrial and residential applications. It is capable of protecting the system against short-circuit currents up to 10kA. It is equipped with a mounting bracket that allows you to remove or install a miniature circuit-breaker even when the phase busbar is installed and is compatible with all GARO busbars for miniature circuit-breakers. MCB GS C-Characteristic 63A 10kA 4-pole

Common characteristics

Wire flexible [mm²]	1-25
Materials	Plast/Plastic
Degree of protection [IP]	20
Colour	Gră/Grey
Frequency [Hz]	50/60
Package size	3
Rated voltage [V AC]	230/400
Tightening torque [Nm]	3,5
Temperature range [C]	-25...+55
Storage temperature [C]	-35...+55
Modules [pcs]	4
Width [mm]	68
Height [mm]	90
Depth [mm]	75

Specific for 2142774

Name	MCB GS C-KAR 63A 10kA 4P
E-Number	2142774
Article Number	2142774
Type designation	MCB GS C463
Rated current [A]	63
Netweight [kg]	0.47

Poles
4
.....
Rated short-circuit cap. [kA]
10
.....
Connection type
Skruv /Screw
.....
Claim prefuse [A]
125
.....
Tripping characteristics
C
.....
Standard
EN 60898-1
.....
Package size [pcs]
3
.....

Accessories list for MCB 10kA 4-pole C-characteristics

Name	E-Number	Article Number	Type designation	Article Description
HJÄLPKONTAKT F MCB	2163216	110184	HLPK F MCB	Hjälpkontakt och signalkontakt för dv ärgbry tare typ MCB GR,MCB GS och MCB GQ.
LÅSBYGEL	2163136	2163136	LB 2	Låsbygel passande MCB GS,RCCB GS,RCBO GS,GCB ,GCBO och de flesta andra komponenter.