

## Product information

00 21 42

### Tool Case "BIG Twin" Electric



- Equipped with 14 KNIPEX tools, a total of 63 brand tools, partly VDE-tested according to DIN EN 60900
- Free-standing in all opening positions thanks to snap-in cover holders with hinge mechanism on both sides, angle freely adjustable
- Can be opened from one or both sides; bottom and lid can be opened independently of each other
- Label field with two stickers for individual labelling
- Max. payload: 25 kg
- Volume: 38 litres
- Heavy duty ABS material, black
- Circumferential aluminium frame with securely mounted, sturdy centre wall that can be fitted on both sides, with versatile inserting options due to elasticated loops and twelve small pockets
- Metal hinges
- Three-digit combination lock for secure locking of the case
- Two metal tilt locks each for fixing the cover and the base
- Removable document compartment and removable tool boards made from dirt-repellent PP twin-wall sheets with 13 tool pockets
- Base tray, can be fixed by press button, height 58 mm, can be subdivided by flexible inserts; cover plate with six large compartments
- With a total of 95 inserting options



#### General

Article No.	00 21 42
EAN	4003773084228
weight	11,550 g
Dimensions	435 x 265 mm
Reach	no
RohS	no




#### Technical details











Dimension exterior (interior) width mm	520 mm (490 mm)
Dimension exterior (interior) height mm	435 mm (370 mm)
Dimension exterior (interior) depth mm	250 mm (110 mm)

#### Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076

#### Content

00 11 01	1 x KNIPEX TwinKey® for all standard cabinets and shut-off systems
08 26 145	1 x Needle-Nose Combination Pliers 
12 42 195	1 x KNIPEX MultiStrip 10 Automatic Insulation Stripper (0,03 – 10,0 mm²) 
13 86 200	1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm²) 

Content	
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool (Ø 8,0 – 13,0 mm) MM
26 26 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers)  $\angle 40^\circ$ 
70 06 160	1 x Diagonal Cutter 
74 06 200	1 x High Leverage Diagonal Cutter 
86 03 180	1 x Pliers Wrench Pliers and a wrench in a single tool 
86 03 180	1 x Pliers Wrench Pliers and a wrench in a single tool 
87 01 180	1 x KNIPEX Cobra® Hightech Water Pump Pliers 
97 53 04	1 x Self-Adjusting Crimping Pliers for wire ferrules with lateral access (0,08 – 10 + 16 mm²) MM 
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (3,5 mm) 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 1) 
98 52	1 x Cable Knife
L240 00055	1 x Knipex Folding ruler Stabila series 400 (200 mm)
101-0300	1 x Picard Locksmith's hammer (300 g)
361 252 1	1 x Rennsteig Electrician's Chisel (250 x 10 mm)
16135	1 x Stabila Spirit Level Type 70 Electric (430 mm)
003760	1 x Wera Joker open-end wrench (10 x 13 mm)
004018	1 x Wera 8100 SA 8 Zyklop set of metal ratchets 28 parts (1/4")
5003484001	1 x Wera 16-part set of VDE interchangeable blades, slim
Accessories	
00 21 42 LE	Tool Case "BIG Twin" empty

technical change and errors excepted

