

Product information

98 99 15

Toolbox "BIG Twin Move RED" Electric Competence



Better safe than sorry: 47 insulated brand tools for work on electrical systems

- Hard-wearing ABS material construction, red; equipped with a range of KNIPEX tools for working on systems, tested according to DIN EN/ IEC 60900
- Telescopic handle set in the base as well as two external, smooth-running skater wheels
- Free-standing in all opening positions thanks to snap-in cover holders with hinge mechanism on both sides, angle freely adjustable
- Can be opened from one or both sides; bottom and lid can be opened independently of each other
- Max. payload: 30 kg
- Volume: 38 litres
- Label field with two stickers for individual labelling
- Circumferential aluminium frame with securely mounted, sturdy centre wall that can be fitted on both sides, with versatile inserting options due to elasticated loops and twelve small pockets
- Metal hinges
- Three-digit combination lock for secure locking of the case
- Two metal tilt locks each for fixing the cover and the base
- Removable document compartment and removable tool board made from dirt-repelling twin-wall PP sheets with 13 tool pockets
- Base tray, can be fixed by press button, height 58 mm, can be subdivided by flexible inserts; cover plate with six large compartments
- Dimensions exterior (W x H x D): 520 x 435 x 290 mm; dimensions interior (W x H x D): 490 x 370 x 110/100 mm
- IEC 60900, DIN EN 60900
- With a total of 95 inserting options

General

Article No.	98 99 15
EAN	4003773084341
weight	15,950 g
Dimensions	432 x 317 mm
Reach	no
RohS	no




Technical details

























Dimension exterior (interior) width mm	520 mm (490 mm)
Dimension exterior (interior) height mm	435 mm (370 mm)
Dimension exterior (interior) depth mm	290 mm (110 mm) / (100 mm)
























Classification

eCl@ss 5.1.4	21100100
ETIM 5.0	EC000181
ETIM 6.0	EC000181
proficl@ss 6.0	EAA404c076

Content

08 26 145	1 x Needle-Nose Combination Pliers 
11 06 160	1 x Insulation Stripper with opening spring, universal (Ø 5,0 mm / 10,0 mm²) 
70 06 160	1 x Diagonal Cutter 

Content	
87 26 250	1 x KNIPEX Cobra® VDE Hightech Water Pump Pliers, insulated (2" / 46 mm) 
95 16 200	1 x Cable Shears with twin cutting edge (Ø 20 mm / 70 mm²)
98 00 10	1 x Open-end wrench (10 mm) 
98 00 13	1 x Open-end wrench (13 mm) 
98 00 14	1 x Open-end wrench (14 mm) 
98 00 17	1 x Open-end wrench (17 mm) 
98 00 19	1 x Open-end wrench (19 mm) 
98 00 22	1 x Open-end wrench (22 mm) 
98 01 10	1 x Box Wrench (10 mm) 
98 01 13	1 x Box Wrench (13 mm) 
98 01 14	1 x Box Wrench (14 mm) 
98 01 17	1 x Box Wrench (17 mm) 
98 01 19	1 x Box Wrench (19 mm) 
98 01 22	1 x Box Wrench (22 mm) 
98 20 25	1 x Screwdrivers for slotted screws (2,5 mm) 
98 20 40 SL	1 x Screwdriver (Slim) for slotted screws (4,0 mm) 
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm) 
98 20 65 SL	1 x Screwdriver (Slim) for slotted screws (6,5 mm) 
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1) 
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2) 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 1) 
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 2) 
98 25 02 SLS	1 x (Slim) PlusMinus screwdriver Pozidriv® (PZ/S 2) 
98 40	1 x T-Handle Drive with driving square 1/2" 
98 42	1 x Reversible Ratchet with driving square 1/2" 

Content	
98 45 125	1 x Extension Bar with internal/external square 1/2"  
98 45 250	1 x Extension Bar with internal/external square 1/2"  
98 47 10	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (10 mm)  
98 47 11	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (11 mm)  
98 47 12	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (12 mm)  
98 47 13	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (13 mm)  
98 47 14	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (14 mm)  
98 47 17	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (17 mm)  
98 47 19	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (19 mm)  
98 47 22	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (22 mm)  
98 47 24	1 x Hexagon Socket for hexagonal screws with internal square 1/2" (24 mm)  
98 52	1 x Cable Knife
98 53 03	1 x Stripping Knives
98 64 02	1 x Insulating clamps plastic 
Accessories	
98 99 15 LE	Tool Case "BIG Twin Move RED" empty

technical change and errors excepted