

Product information

71 31 160

KNIPEX CoBolt® S

Compact Bolt Cutters

With recess in the cutting edge



Tiny titan with 25-fold leveraging of hand strength – just right for round material

- Heavy-duty cutting edge with recess slices through the hardest round materials in only one cutting action
- Extremely high cutting performance in a convenient length of 160 mm
- Small, slim head for excellent accessibility
- Compact and powerful: cuts bolts, nails, rivets etc. up to Ø 4.8 mm
- Cutting edge hardness approx. 64 HRC
- Less physical effort due to efficient lever action mechanism
- Slippage of cutting material reduced by lasered cutting edge
- With gripping surface below the joint for gripping and pulling wires from Ø 1.0 mm
- Blades with recess for easier cutting of larger cross-sections thanks to better leverage close to the fulcrum
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

General

Article No.	71 31 160
EAN	4003773084587
Pliers	black atramentized
Handles	plastic coated
weight	200 g
Dimensions	160 x 45 x 14 mm
Reach	no
RohS	no

Technical details

Cutting capacities soft wire (diameter)	Ø 5.3 mm
Cutting capacities medium hard wire (diameter)	Ø 4.8 mm
Cutting capacities hard wire (diameter)	Ø 3.6 mm
Cutting capacities piano wire (diameter)	Ø 3.3 mm

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002689
ETIM 6.0	EC002689
proficl@ss 6.0	AAA949c004

technical change and errors excepted

