

Product information

95 16 160

KNIPEX StepCut

IEC 60900 DIN EN 60900



⚡ 1000 V



Cable cutting made easy: innovative step cutting separates wires one by one to save energy

- Small, light, strong: comfortable cutting without crushing and just 160 mm in size
- Noticeably less effort: the gradations cut wires one after the other; cutting is up to 40% easier than with standard cable shears of the same length!
- Ergonomic handle design: optimal cutting feel even for larger cable diameters
- Cuts multi-core stranded copper and aluminium cables up to Ø 15 mm (50 mm²)
- Cuts solid copper and aluminium cables up to 5 x 4 mm²
- Cuts without crushing
- Bolted joint: precise, effortless, durable
- Cutting edges additionally induction-hardened
- Pinch guard fitted for safe work
- Not suitable for steel wire and hard drawn copper conductors
- High-grade special tool steel, forged, oil-hardened

General

Article No.	95 16 160
EAN	4003773085966
Shears	chrome plated
Handles	insulated with multi-component grips, VDE-tested
weight	225 g
Dimensions	160 x 60 x 28 mm
Standard	DIN EN 60900 IEC 60900
Reach	Nein
RohS	no

Technical details

Cutting capacity copper cable, multiple-stranded	50 mm ²
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
AWG	1 / 0
VDE tested	yes

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000142
ETIM 6.0	EC000142
proficl@ss 6.0	EAD256c001

technical change and errors excepted

