

## Product information

# 97 52 18

### Crimping Pliers

Also for two-hand operation



- The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Two-hand operation for easy crimping of large conductor diameters
- Easy handling as a result of well balanced centre of gravity, angled head and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened

### General

Article No.	97 52 18
EAN	4003773026839
Pliers	burnished
Head	burnished
Handles	with non-slip plastic coating
weight	571 g
Dimensions	250 x 78 x 26 mm
Reach	no
RohS	no

### Technical details



Applications	Twin wire ferrules 2x6 / 2x10 / 2x16 mm <sup>2</sup>
AWG	2 x 10 / 2 x 8 / 2 x 6

### Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003

*technical change and errors excepted*



