

## Product information

# 97 90 15

## Crimp Assortment


For wire ferrules

- With crimping pliers for wire ferrules 97 53 09 and automatic insulation stripper KNIPEX PreciStrip16 12 52 195
- In a TANOS MINI-systainer® (solid plastic box)
- Two stackable plastic inserts with 6 trays each for connectors
- With an assortment of wire ferrules with/without collar
- T-Loc fastener for one-handed operation: open or close the systainer® with one turn and connect to a second systainer®



General	
Article No.	97 90 15
EAN	4003773084877
weight	1,450 g
Dimensions	170 x 67 mm
Reach	no
RohS	no

Classification	
eCl@ss 5.1.4	27400218
ETIM 5.0	EC000524
ETIM 6.0	EC000524
proficl@ss 6.0	EAB559c013

Content	
12 52 195	1 x KNIPEX PreciStrip16 Automatic Insulation Stripper (0,08 - 16 mm <sup>2</sup> )
97 53 09	1 x Self-Adjusting Crimping Pliers for wire ferrules with front loading (0,08 – 10 + 16 mm <sup>2</sup> ) 
	100 x Twin wire ferrules with plastic collar (2 x 1,5 mm <sup>2</sup> )
	80 x Twin wire ferrules with plastic collar (2 x 2,5 mm <sup>2</sup> )
	40 x Twin wire ferrules with plastic collar (2 x 4,0 mm <sup>2</sup> )
	30 x Twin wire ferrules with plastic collar (2 x 6,0 mm <sup>2</sup> )
	20 x Twin wire ferrules with plastic collar (2 x 10,0 mm <sup>2</sup> )
	150 x Wire ferrules with plastic collar 14 / 8 mm (1,5 mm <sup>2</sup> )
	100 x Wire ferrules with plastic collar 14 / 8 mm (2,5 mm <sup>2</sup> )
	80 x Wire ferrules with plastic collar 17 / 10 mm (4 mm <sup>2</sup> )



**Content**

	50 x Wire ferrules with plastic collar 20 / 12 mm (6 mm <sup>2</sup> )
	35 x Wire ferrules with plastic collar 22 / 12 mm (10 mm <sup>2</sup> )
	20 x Wire ferrules with plastic collar 24 / 12 mm (40 x 16 mm <sup>2</sup> )

*technical change and errors excepted*

*Systainer® is a registered trademark of TANOS GmbH*