

Product information

98 24 02 SL

Screwdriver (Slim) for cross-recessed screws

Phillips®

IEC 60900 DIN EN 60900

- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000V ⚡

General

Article No.	98 24 02 SL
EAN	4003773079767
point	burnished
Handles	insulating multi-component handle, VDE-tested
weight	94 g
Dimensions	212 x 33 x 35 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Size	PH2
Blade length	100 mm
Handle length	112 mm
Length of non-insulated blade	18 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040401
ETIM 5.0	EC000144
ETIM 6.0	EC000144
proficl@ss 6.0	AAA818c006
UNSPSC 13.1	27111701

technical change and errors excepted

Phillips® is a registered trademark of Phillips Screw Company