

Product information

98 25 01 SLS

(Slim) PlusMinus screwdriver

Pozidriv®

IEC 60900 DIN EN 60900

- Driving tips for PlusMinus profile screws
- Use with electronics installation components, e.g. automatic circuit breakers
- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000 V ⚡

General	
Article No.	98 25 01 SLS
EAN	4003773081050
point	burnished
Handles	insulating multi-component handle, VDE-tested
weight	55 g
Dimensions	187 x 28 x 30 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no
Technical details	
Size	PZ/S 1
Blade length	80 mm
Handle length	107 mm
Length of non-insulated blade	15 mm
VDE tested	yes
Classification	
eCl@ss 5.1.4	21040401
ETIM 5.0	EC000144
ETIM 6.0	EC000144
proficl@ss 6.0	AAA818c006
UNSPSC 13.1	27111701

technical change and errors excepted

Pozidriv® is a registered trademark of European Ind. Serv. Ltd.

