

VEC02

Untethered EV Charger

DATA SHEET





The UK's most affordable EV charger for powering your business.

With more than 1 in 10 of new vehicles being electric and their numbers increasing rapidly each year, it's time to join the EV revolution. Whether you want to cater to your tenants, customers, employees, or visitors, there's no denying that the future is electric. The good news is that we're here to make adopting EV technology a breeze. We'll help you choose the right EV charger for your specific requirements and offer engineer support within 48 hours of installation to ensure complete peace of mind. Our EV chargers are suitable for a variety of locations, from car parks and public spaces to workplaces, development sites, and even theme parks.

Our universal three-phase VEC02 is an affordable EV and PHEV compatible charger that is designed for a three-phase power supply, which is suitable for commercial environments such as the workplace. With its fast-charging capabilities, you can charge your EV nearly three times faster when compared with a standard 7.4kW charger. The VEC02 charger is both cost-effective and efficient. It's a sleek and compact unit that offers an excellent solution for charging Type 1 and Type 2 EVs.

Product features

- Type 1 & Type 2 universal charging port
- Charge your vehicle at up to 22kW's
- Cost-effective and compact
- Share your charge point and start earning money through Monta
- Built-in LED lights that display charging status and error messages
- Built-in PEN Protection
- Built-in RCD- 30 milliamp Type A, 6 milliamp DC
- Full OCPP 1.6J protocols including smart charging
- Load Balancing
- Set-up and monitor your charger easily through the evec app
- Corrosion-resistant and fire retardant
- IP54 rated dust and weatherproof
- CE and UKCA approved



Superfast charging

Available up to 22kW for incredibly fast charging. Our pedestal is compatible with all EVs and PHEV to get all vehicles ready in record time!



Easy to use

Control your charger easily via our mobile app, plug & charge or via our approved pay-to-charge partner, Monta.



OZEV approved

Get a grant of up to £14k (£350 per socket) for up to 40 charge points with the OZEV workplace charging scheme.



Safe

All of our chargers also come with PEN protection, security breach notifications and over the air updates.



Cost effective

Our chargers are the most affordable in the UK and are designed for everyone, no matter your budget.



Speedy delivery

Get setup quickly with next day delivery across our charger range.

Model: VEC02
Input

Power Supply	3P+N+PE
Rated Voltage	AC400±10%
Rated Current	32A(16A ,13A,10 Adjustable)

Output

Output Voltage	AC400±10%
Maximum Current	32A(16A ,13A,10 Adjustable)
Rated Power	22KW(MAX)

User Interface

Charger Connector	Type 2 socket
Cable length	N/A
Material	ABS + PC
Colour	Black
Three colour LED	•
OLED	Optional
Start mode	•
Plug and charge	•
OCPPI.6 Ethernet	•
evec app	•

Safety

Ingress Protection	IP54
Impact Protection	•
Over Current Protection	•
Residual Current Protection (AC30mA,DC6mA)	•
PEN Protection	•
Over/Under Voltage Protection	•
Over Temperature	•
Certification	CE / UKCA
Certification Standard	EN IEC 61851, EN 62196

Environment

Installation	Wall mounted
Mounting Options	Floor posts available
Work Temperature	-25°C ~ 50°C
Work Humidity	3% ~ 95%
Work Altitude	<2000m

Package

Production Dims (H*W*D)mm	300*190*105
Package Dims (L*W*H)mm	349*239*178
Net weight (kg)	1.8
Gross weight (kg)	2.3

Powered by Monta

evec's chargers are now included in the Powered by Monta program and will be shipped with pre-installed Monta software. This will make the process of joining Monta's platform easier for charge point owners, whether they are residential or commercial. The Monta platform allows charge point owners to make money by sharing their charging points with the EV charging community. Owners have complete control over the charging point's availability, cost, and accessibility, delivering an adaptable solution for all charge point owners. Monta's roaming network of more than 300,000 charging points across Europe will be available for use by evec's customers, enabling drivers to charge their vehicles at home, on-the-go, and at work.

Accessories

SKU	Item Description
ECB01	Cable Bag for Electric Vehicle Charger Cables
CT-Clamp	CT Clamp – with 5m cable
ECH01	Cable Holder For Electric Vehicle Chargers
ECL01	11 - 22kW EV Commercial Charging Cable, Triple Phase, Type 2, 5m Length

You may also like...

Our 22kW tethered domestic charger, or our 22kW Pedestal Charger



VEC04 Tethered 22kW EV Charger

- ✓ Compatible with Type 2 EVs
- ✓ Tough & Durable
- ✓ Easy to setup and control via the evec app



22kW Pedestal EV Charger

- ✓ Compatible with Type 1 & Type 2 EVs
- ✓ Customisable
- ✓ Light for better visibility
- ✓ Tough & Durable
- ✓ Easy to setup and control via the evec app



evec
for everyone

www.evec.co.uk

0161 2496 780
sales@evec.co.uk

Unit 8 Fourways Trading Estate,
Trafford Park, Manchester, M17 1SW

