

Datasheet

Manufacturer Part No.: T24CA056 ... T24CA065

Hook-and-Loop Cable-Tie Set Item-No.: T24CA056 ... T24CA059 5 m-Roll Item-No.: T24CA060 ... T24CA065



These hook-and-loop cable-ties made of polyamide are easy to open and close again. Therefore, they are ideally suited for general bundling tasks and fixations of, for example, objects, cables, sports utensils, plants, curtains, tools and much more. The excellent material properties of polyamide allow a wide range of applications as far as environmental conditions are concerned. The material is dimensionally stable, robust and resistant to many liquids and also UV radiation. The supply set of 10 hook-and-loop cable ties with eyelet content is optimal for any indoor and outdoor applications. The black design can be unrestricted and inconspicuous in many usages.



Technical data: Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: black • RoHS compliant, REACH compliant.

Part-No.	Description	Length	Width	Color	Content	EAN / GTIN
T24CA056	Hook-and-loop cable-ties 100 x 12 mm Set	100 mm	12 mm	Black	100 pcs.	4260732286219
T24CA057	Hook-and-loop cable-ties 150 x 12 mm Set	150 mm	12 mm	Black	100 pcs.	4260732286226
T24CA058	Hook-and-loop cable-ties 200 x 12 mm Set	200 mm	12 mm	Black	100 pcs.	4260732286233
T24CA059	Hook-and-loop cable-ties 50x 150 + 50x 200 mm Set	150/200 mm	12 mm	Black	100 pcs.	4260732286240



Part-No.: T24CA060 ... T24CA065 – Hook-and-loop-tape without buckles for flexible use and cutting

Technical data: Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: versions see below • RoHS compliant, REACH compliant.

Part-No.	Description	Length	Width	Color	Content	EAN / GTIN
T24CA060	Hook-and-loop tape 5 m x 20 mm Roll Black 5 m	5 m (one piece)	15 mm	Black	5 m	4260732286257
T24CA061	Hook-and-loop tape 5 m x 20 mm Roll Green 5 m	5 m (one piece)	15 mm	Green	5 m	4260732286264
T24CA062	Hook-and-loop tape 5 m x 20 mm Roll Red 5 m	5 m (one piece)	15 mm	Red	5 m	4260732286271
T24CA063	Hook-and-loop tape 5 m x 20 mm Roll Yellow 5 m	5 m (one piece)	15 mm	Yellow	5 m	4260732286288
T24CA064	Hook-and-loop tape 5 m x 20 mm Roll White 5 m	5 m (one piece)	15 mm	White	5 m	4260732286295
T24CA065	Hook-and-loop tape 5 m x 20 mm Roll Blue 5 m	5 m (one piece)	15 mm	Blue	5 m	4260732286301