

Data Sheet

PVC Twin Cable, 2 x 0.5 mm², 10 M, Grey



Technical data

Jacket, outer dimension: PVC 4.0 x 2.0 mm

AWG: 20

No. of conductors: 2 x 0.5 mm²

CCA strand per conductor: 16 x 0.20 mm

Color: Grey

Capacitance conductor: 210 pF

Voltage: Less than 50 V/DC or 75 V/AC

Insulation resistance: Min 200 MΩ x km

Operating temperature: -20 °C to 70 °C

Operating humidity: 10 - 90 % RH

Packaging: 10 meter spool