

ZCKY51

limit switch lever ZCKY - metal square rod lever
3 mm L=125 mm - -40..120 °C



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ
Associated head	ZCKE05
Movement of operating head	Rotary
Type of operator	Rod lever spring return metal (square rod 3 mm, L = 125 mm)
Type of approach	Lateral approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C for standard environment -40...70 °C for low temperature 10...120 °C for high temperature
Ambient air temperature for storage	-40...70 °C for standard environment -40...70 °C for low temperature 10...120 °C for high temperature
Environmental characteristic	High temperature Low temperature Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0922 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations