

ZCY49

limit switch lever ZCY - thermoplastic roller
lever Ø 50 mm variable length



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKD XCKP XCKT
Associated head	ZCE01 ZCE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic (variable length, roller diameter 50 mm)
Tracks	No track
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations