


Rating	10A 24VDC	Mounting Hole	Circuit	
Contact Resistance	50m ohm Max.			
Insulation Resistance	DC 500V 100M ohm Min.			
Dielectric Strength	AC 1500V 1 minute			
Operation Temperature	-20°C ~ 85°C	Thickness	X	Y
Switch Function	2P SPST ON-OFF	0.75...1.25	19.2-0.1	13+0.1
		1.25...2	19.4-0.1	13+0.1
		2...3	19.8-0.1	13+0.1



Date	Name	Descriptions			NO	
Drawn	Checked	Approved	SCI No.	Model Name	ROCKER SWITCH	
黄平平	杨金江		Customer No.	Model No.	R13-70A-01	REV.
04/29/08	04/29/08		Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.	
						0