


Rating	16A 125V AC 1/8HP	Mounting Hole	Diagram	
	10A 250V AC 1/3HP cULus			
Contact Resistance	50m ohm Max.			
Insulation Resistance	DC 500V 100M ohm Min.			
Dielectric Strength	AC 1500V 1 minute			
Operation Temperature	-20°C~85°C	Panel Thickness		
Switch Function	3P SPST ON-OFF (Illuminated)	X	Y	
		0.75...1.25	19.2-0.1	13+0.1
		1.25...2	19.4-0.1	13+0.1
		2...3	19.8-0.1	13+0.1

\* Material  
 Frame: Nylon#66, Black  
 Actuator: PC  
 Terminal: Copper alloy , Silver plated



1820555	Green Clear
1820545	Yellow Clear
1820532	Red Clear
SCI NO.	Lens Color

						△
						△
Date	Name	Description				NO
Drawn	Checked	Approved	SCI No.	SEE TABLE	Model Name	ROCKER SWITCH
邵勇	研登部		Customer No.		Model No.	R13-70B-01
06/26/'07	邵勇		Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.	