




Rating	10(4)A 250V~	Mounting Hole
	16A 125V AC	
	10A 250V AC	
	10A 28VDC	
Contact Resistance	50m ohm Max.	 Panel Thickness 2.0~3.0 mm
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temperature	-20°C~125°C	
Switch Function	2P SPST ON-OFF	
		 Panel Thickness 0.7~3.0 mm







*Material

Frame: Nylon#66,Black

Actuator: Nylon#66,Black

Terminal: Copper alloy,Silver plated

Diagram



							△
							△
Date	Name	Description					NO
Drawn	Checked	Approved	SCI No.	1821032	Model Name	ROCKER SWITCH	
鐘燕康	研發部 關永強		Customer No.		Model No.	R13-208A-02	
8/23/'07	李元生		Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		