














Rating	10(4)A 250V~ 	Mounting Hole
	16A 125V AC 10A 250V AC 	
	10A 28VDC 	
	6A 14VT	
Contact Resistance	50m ohm Max.	
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temperature	-20°C~85°C	
Switch Function	3P SPST ON-OFF (Illuminated)	



***Material**

Frame: Nylon#66,Black
 Lens: PC, Green clear
 Terminal: Copper alloy,Silver plated



									△
									△
Date	Name	Description							NO
Drawn	Checked	Approved	SCI No.	1821124	Model Name	ROCKER SWITCH			
鐘燕康			Customer No.		Model No.	R13-208B-02			
8/23/'07			Unit	mm	 SHIN CHIN INDUSTRIAL CO., LTD.				