













Rating	10(4)A 250V~ 	Mounting Hole
	16A 125V AC 10A 250V AC 	
	10A 28VDC 	
	6A 14VT	
Contact Resistance	50m ohm Max.	
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temperature	-20°C~85°C	
Switch Function	2P SPST ON-(OFF)	



\*Material  
 Frame: Nylon#66,Black  
 Actuator: Nylon#66,Black  
 Terminal: Copper alloy,Silver plated

Diagram



							△
							△
							NO
Date	Name	Description					
Drawn	Checked	Approved	SCI No.	1821156	Model Name	ROCKER SWITCH	
鍾燕康			Customer No.		Model No.	R13-208E-02	
8/23/'07			Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.		