






Rating	3A 125V, 1A 250V AC 	Mounting Hole	Circuit
Contact Resistance	50m ohm Max.		
Insulation Resistance	DC 500V 100M ohm Min.		
Dielectric Strength	AC 1500V 1 minute		
Switch Function	2P SPST OFF-(ON)		

Material:  
 Bottom: Black, ABS  
 Button: Black, Red, ABS  
 Printed: None



SCI BOM NO	BUTTON
1830112	Black
1830258	Red

						△	
						△	
<b>Date</b>		<b>Name</b>		<b>Descriptions</b>		<b>NO</b>	
<b>Drawn</b>	<b>Checked</b>	<b>Approved</b>	<b>SCI BOM No.</b>	See the table	<b>Model Name</b>	PUSH SWITCH	
李日紅	<i>[Signature]</i>		<b>Customer No.</b>		<b>Model No.</b>	R13-83A-05	REV.
05/13/09	<i>[Signature]</i>		<b>Unit</b>	mm	 SHIN CHIN INDUSTRIAL CO., LTD.		0