



Rating
16A 125V AC 10A 250V AC
Contact resistance
50mΩ Max
Insulation resistance
DC 500V 100MΩ Min
Dielectric strength
AC 1500V 1 minute
Cut-out

	X	Y
	X	Y
0.75-1.25	26.7-0.1	25.8+0.1
1.25-2	26.9-0.1	25.8+0.1
2-3	27.3-0.1	25.8+0.1

FEATURES

- * MATERIAL: Frames are nylon (UL flame: 94V-2). Terminals are silver plated brass.
- * Illuminated actuators are molded in PC, available with red, amber and green colors.
- * Snap-in mounting, easy to install switch into panel.

R13- [] [] [] - [] []

ROCKER	FUNCTION		TERMINAL
1 0 4 	A 4P DPST	H 6P DPDT	0 1 .250" SQ
1 0 5 	B 4P DPST (ILLUMINATED) 125V AC 33KΩ / 250V AC 150KΩ	I 6P DPDT	
	C 6P DPDT		
	D 6P DPDT		

R13-104A-01
 R13-105B-01
 R13-104B-01